

# **ISO-UXX** Isolating & Protecting USB Connections



The ISO-Uxx devices offer isolation called *ground lift* in audio applications, and *galvanic isolation* in electrical engineering. This isolation eliminates noise and interferences, ensuring clean signal transfer and precise data transmission between host PC and USB device. The ISO-Uxx devices have superior quality and are easy to use.

#### Note

The ISO-Uxx devices are not intended for use as protection against voltages hazardous to health.

## **Safety Specifications**

The ISO-Uxx devices are tested according to EN 62368-1 and withstand the following voltages for 60 seconds between their inputs and outputs:

Device	<b>DC Isolation</b>	<b>AC Isolation</b> <sup>1</sup>
ISO-U11	2000 V	500 V
ISO-U20	2000 V	500 V
ISO-U30	5000 V	3000 V

The ISO-Uxx devices effectively block overvoltages from crossing from one side to the other. However, the electronics of the ISO-Uxx devices themselves may be irreversably damaged when exposed to voltages higher than 5.5 V.

<sup>1</sup>Rated at 50 Hz

### **USB Data Transfer Rates**

The ISO-Uxx devices cover a wide range of USB speeds up to USB 3.0 SuperSpeed with 5 Gbit/s:

USB specification	ISO- U11	ISO- U20	ISO- U30
USB 1.1 Full Speed (12 Mbit/s)	1	$\checkmark$	$\checkmark$
USB 2.0 Hi-Speed (480 Mbit/s)		$\checkmark$	1
USB 3.0 SuperSpeed (5 Gbit/s)			1

#### **Power & Current Limits**

When powered correctly, the LED indicator on the ISO-Uxx devices lights up. ISO-Uxx and attached USB devices are powered solely via USB, no external power adapter is needed.

Typical currents the ISO-Uxx devices can supply on their output are listed below. For the ISO-U11 and ISO-U20, it is assumend that the host can provide a minimum of 500 mA on the input, respectively 900 mA for the ISO-U30.

Device	l <sub>out,typ</sub>	USB device speed
ISO-U11	390 mA	Full Speed
ISO-U20	340 mA	Hi-Speed
ISO-U30	710 mA	Hi-Speed
	660 mA	SuperSpeed

# **Operational Details**

All ISO-Uxx devices come in a rugged aluminum enclosure. Rubber seals ensure a firm stand. ISO-U11 and ISO-U20 measure 57x45x28 mm, while the ISO-U30 slightly larger at 67x45x28 mm.

The ISO-Uxx devices contain no servicable parts. They can be operated in environments with temperatures between -40 °C and +40 °C. No driver or special software is required.

ISO-Uxx devices are not certified for medical use.